

## **Ozone Technology Comparison Chart**

| FEATURE  | DPD                                  | MEMBRANE                              | KUNTZE                       | KUNTZE ADVANTAGE  |
|--|--------------------------------------|---------------------------------------|------------------------------|---|
| Sensor<br>Technology                           | Colorimetric                         | Membrane<br>Sensor<br>Amperometric    | Bare Sensor<br>Amperometric  | High confidence in chlorine measurement   |
| Sensor Cleaning                                | No                                   | No                                    | (ASR)®                       | Labor <u>reduction</u>  |
| Replacement<br>Membrane Cap                    | N/A                                  | Yes                                   | No                           | Remove replacement part, gain more durable measurements                                       |
| Reagents/<br>Electrolyte                       | Yes                                  | Yes                                   | No                           | No waste stream, less cost  |
| Consumables                                    | Yes                                  | Yes                                   | No                           | Labor <u>reduction</u> , less cost  |
| Response Time<br>After 0mg/I Of O <sub>3</sub> | Interval Based -<br>150 Seconds      | Will Not Respond<br>As Expected       | t90 = 20 seconds             | Sensor does not go to sleep when exposed to extended periods of time with low Cl <sub>2</sub> |
| Bubble Influence                               | Yes                                  | Yes                                   | No                           | Confidence in chlorine measurement  |
| Scheduled<br>Replacement<br>Parts              | 30 Days                              | 90 Days                               | > 365 Days                   | Reduce time required to provide routine service   |
| Service  | Strongly recommends service contract | No - but service contract recommended | No service contract required | Reduce need to rely on third party's schedule, cost reduction                                 |
| Sample Line<br>Flow Control                    | Yes                                  | No                                    | Yes                          | Eliminates potential fluctuations, resulting in confident monthly reports                     |
| Pressure                                       | < 2 psi                              | < 5 psi                               | Up to 87 psi                 | Not pressure sensitive  |

Sales Inquiries: support@kuntze.com 724-339-8510 www.kuntze.com

